

## Leica 3D Disto

### Tablet & Wi-Fi requirements



- **Operating systems**

Windows 7 or higher.

Not supported Windows 10 S, RT and modified editions.

- **Processor**

minimum i3, i5 or i7

**Important:** ARM 64 based processors like Microsoft® SQ1™ (built in **Microsoft® Surface Pro X**) are **not compatible** with the Leica 3D Disto software for Windows®

- **Screen and resolution**

At least 1000 x 680 pixels, desktop or touch screen

- **Wi-Fi and data transfer**

3D Disto with serial number starting with 175 or 177 need an external USB - Wi-Fi stick.

We recommend **TP-Link TL-WN823N**.

3D Disto with serial number starting with 176 can be connected directly to the tablet integrated Wi-Fi.

A USB port “Type A” is the most comfortable for the Wi-Fi stick and for data transfer.

Please use an adapter for tablets with mini-USB or micro-USB port.

**Important:** USB port and adapter need to have “on-the-go” functionality (OTG)!



- **Recommended Windows tablet:**

Microsoft Surface Pro 6 – i5, 12”, Windows 10 Home or Professional